

## DC/DC converters 3–300 Watt 4:1 | 12:1

### FEATURES

- EN50155 Railway Approvals
- Extended Temperature range: -40°C to +85°C
- Ruggedized designs, EN61373 compliant for shock & vibration
- Ultra wide input voltage range: 9–36, 18–75, 43–160, 14–160 VDC
- Suitable for Applications in Harsh environment

- RIA 12 Surge Filters
- 3-year warranty

### STANDARDS AND DIRECTIVES

- IEC/EN/UL 60950-1
- IEC/EN/UL 62368-1
- EN 45545-2
- RIA 12, NF F 01-510

### RAILWAY DC/DC CONVERTERS

SIP



3–6 W

DIP



8–200 W

Chassis assembly



20–300 W

3 100 200 300  
PERFORMANCE IN WATTS

